



PICOSECOND DUAL-WAVELENGTH FIBER-LASER FOR CARS & SRS MICROSCOPY



Aunion turnkey laser sources for nonlinear microscopy deliver synchronized picosecond pulses with a tunable wavelength difference. They are completely software controlled and available with either a free-space output or a single fiber end. Due to the all-fiber pulse generation and frequency conversion, maximum compactness and alignment-free operation can be realized.

APPLICATIONS

- CARS spectroscopy and microscopy
- Microscopic multi-modal nonlinear imaging (CARS, SHG, TPEF)
- SRS microscopy



Multimodal composite image of human connective tissue showing an overlay of CARS (red), SHG (blue) and TPEF (green) signals. Courtesy of IPHT Jena

PICOSECOND DUAL-WAVELENGTH FIBER-LASER FOR CARS & SRS MICROSCOPY

	FOPG-VERSION FOR CARS	FOPO-VERSION FOR CARS & SRS
Tuning range (continuous)	2700 cm ⁻¹ ... 3300 cm ⁻¹	930 cm ⁻¹ ... 3300 cm ⁻¹
Tuning speed	<1 s (full range)	< 2 s (full range)
Output wavelength 1	1025 nm ... 1040 nm	1025 nm ... 1050 nm
Output wavelength 2	770 nm ... 810 nm	770 nm ... 960 nm
Spectral width wavelength 1 (FWHM)	< 15 cm ⁻¹	< 5 cm ⁻¹
Spectral width wavelength 2 (FWHM)	< 40 cm ⁻¹	< 6 cm ⁻¹ @ 770 - 850 nm < 20 cm ⁻¹ @ 850 - 960 nm
Repetition rate wavelength 1 (FWHM)	1 MHz ... 3 MHz	18 MHz
Repetition rate wavelength 2 (FWHM)	1 MHz ... 3 MHz	9 MHz
Pulse duration	< 30 ps	< 10 ps @ 770 - 850 nm < 20 ps @ 850 - 960 nm
Average power wavelength 1	> 100 mW @ 1 MHz > 300 mW @ 3 MHz	> 200 mW
Average power wavelength 2	> 10 mW @ 1 MHz > 30 mW @ 3 MHz	> 50 mW
Peak power wavelength 1	> 1 kW	> 0.5 kW
Peak power wavelength 2	> 1 kW	> 0.5 kW
RIN of wavelength 1 @ 9 MHz	Not applicable	< -145 dBc
Polarization		Linear
Beam quality		M ² < 1.2
Dimensions (width x depth x height)	260 mm x 320 mm x 150 mm	560 mm x 410 mm x 140 mm
Mass	< 15 kg	< 35 kg
Power connection		230 V
Cooling		Air-cooled
Output	Fiber coupled	Free space

