LDD605 Laser Diode Driver



The LDD605 laser diode driver is a combination current and temperature controller with sophisticated front-panel menu operation and plain text computer command interface via ethernet and USB. A high-precision low-noise current source drives a wide range of diodes at up to 6 amps. The precision temperature controller, with flexible computer-defined PID response, provides 60 W capacity for a wide range of TEC devices. The LDD605 is designed for use with our MOA series of tapered amplifiers and high-power diodes for lasers and fibre amplifiers.

Features

- Low noise diode driver, 6 A at up to 6 V
- Precision temperature controller
- Fully adjustable digital PID temperature servo
- Peltier TEC driver, 60 W
- Current modulation, 40 kHz bandwidth
- External control via USB and ethernet
- Text command

Applications

- Laser cooling and trapping
- Bose-Einstein condensation
- Quantum optics: pump-probe
- Electromagnetic transparency and slow light
- Time and frequency standards
- Laser spectroscopy
- Physics teaching labs

Laser Diode Driver

Specifications LDD605 Rev 0.20

Current	
Output current	LDD: 0 – 6A, \pm 1mA display/set point resolution
Set-point accuracy	<0.5% Error
Noise	TBD
Compliance voltage	Max diode voltage 6V@6A
External modulation	0 – 40kHz (–3dB), 10mA/V, max 10Vp-p
Temperature	
Range	-20°C to +80°C, ±0.01°C display/set point resolution
Set-point accuracy	±5 mK/°C
TEC power	±5A, ±12V (60W)
Stability	±5mK/°C
Sensor	NTC 10k Ω (provided), reads °C in all cases
Computer interface	
Ethernet	10/100 TP, RJ45
USB	USB2.0, plug type USB-A
Safety Features	
Кеу	Front panel key required for laser operation
Interlock	Rear interlock (3.5mm mono jack) for quick laser current disable
Current limit	Laser current limit to avoid accidental diode over current
Temperature limit	High and low limits on temperature to ensure safe operation
Power and dimensions	
	100/110/120V or 220/240V 50/60 Hz 14
Dimensions	250 mm x 79 mm x 292 mm (WxHxD) 2.4 kg
Dimensions	250mm x / 5mm x 252mm (WXNXD), 2.4Kg
General	
Current connector	DE15 high density - 15 pin connector
Temperature connector	DE9 - 9 pin connector
Display type	128 x 64 LCD Graphic Display

MOG Laboratories Pty Ltd Stes 34-35, 49 University St Carlton VIC 3053 Australia Tel: +61 3 9939 0677 info@moglabs.com MOGLabs USA 419 14th St Huntingdon, PA 16652 USA Tel: +1 814 251 4363 info@moglabsusa.com MOGLabs Europe Goethepark 9 10627 Berlin Germany Tel: +49 30 21 960 959 info@moglabs.eu

© 2017 MOG Laboratories Pty Ltd

Product specifications and descriptions in this document are subject to change without notice