


# CYDECECAC

- HIGH-RESOLUTION AND HIGH-SPEED 3D SCANNING SYSTEM
- 150 MM SCANNING AREA
- USER FRIENDLY CONCEPT
- SOPHISTICATED ANALYSIS AND AUTOMATION SOFTWARE




Coplanarity of BGA components



Roughness on solar wafer

Solid Oxid Fuel Cell (SOFC)

By courtesy of: Forschungszentrum Jülich



### OVERVIEW

The cyberSCAN CT 100 is a compact high resolution non-contact profilometer. The main components of the system are a laser or a white light sensor and a x-, y-motion system on a granite platform. Especially the chromatic white light sensors combine high accuracy and high measurement speed. The sensors are available with a resolution down to 3 nm and a measurement range up to 25 mm. The system can scan a maximum area of 150 mm x 150 mm. The proprietary and userfriendly cyberTECHNOLOGIES Software offers sophisticated surface metrology analyses and automated measurement routines.

### APPLICATIONS

Typical applications are the analysis and quality control of printing processes, such as thick-film measurement on a variety of substrate materials, volume measurement of paste depots, epoxy-films, dots or other printed and dispensed features. Geometry and position measurement of highly contoured objects like solder bumps, microlenses, and MEMS devices, as well as flatness and coplanarity analysis are other popular applications.

- Printed products, systems or devices
- Device packaging
- Printed circuits
- MEMS
- Fuel cell elements
- Soft and transparent materials or coatings
- Solar cells
- Medical devices

### SOFTWARE

The proprietary cyberTECHNOLOGIES, Windowsbased software package SCAN SUITE combines system control, data collection and data analysis in a user friendly interface. Comprehensive profile, 3D and roughness analyses conforming to DIN ISO are included. The software can handle up to 10.000 x 10.000 data points in one scan.

An outstanding feature is the ASCAN Software:

- Automation of measurement routines
- Easy programming using tasks and templates
- Offset and fiducial correction
- Built-in SPC Charts with reporting function
- Flexible, user defined data output formats
- Barcode or user field input
- Step & Repeat function

### **TECHNOLOGY**

- Fast and accurate magnetic linear stage
- Measurement speed: 2 kHz (4 kHz)
- 150 mm travel in x- and y-direction, lateral resolution 0.05 μm
- 2D profiles and 3D topographical maps
- Large scanning area, up to the maximum travel of 150 mm at maximum x-, y-, z-resolution
- Laser confocal and chromatic white light sensors
- Resolution down to 3 nm, measurement range up to 25 mm
- Optional high resolution camera




### SYSTEM INCLUDES

- CT 100 base unit with manual z- and motorized x- and y-stage
- One sensor of choice (see sensor specifications)
- High resolution off-axis camera including LED illumination
- External system controller with USB interface
- PC Workstation (current version)
- Factory installed Windows 7 64-bit and cyberTECHNOLOGIES SCAN SUITE license
- 22" widescreen monitor, keyboard, mouse
- Reference manuals and user guides

### OPTIONS

- ASCAN Software for automation of measurement tasks and analyses, 2D and 3D, Step & Repeat
- High speed sensor controller (4 kHz)
- Additional sensors
- Traceable calibration tools and certification targets
- Vacuum chucks (porous ceramics)



## **SPECIFICATIONS**

DIMENSIONS				
(L	Χ	W	Χ	H)

WEIGHT

SYSTEM CONTROLLER

WORKSTATION PC

CONNECTIONS

POWER REQUIREMENTS

OPERATING TEMPERATURE

MEASUREMENT SURFACE SIZE

LINEAR ENCODER RESOLUTION

MINIMUM LATERAL RESOLUTION

TRAVEL LIMITS IN X AND Y (MOTORIZED)

TRAVEL LIMIT IN Z (MANUAL)

MAXIMUM LOAD ON PLATFORM

AVAILABLE SENSORS

450 x 350 x 450 [mm] (17 x 14 x 16 [in])

44 kg (97 lbs)

Includes Motion Control, Sensor Controller
(2 kHz), Power Supplies, USB Interface to Workstation

Inquire about current specifications,
22" widescreen monitor

Ethernet, DVD Drive, USB (front and back side), Parallel Port, Keyboard, Mouse, DVI and Analog Video Output

100-240 V AC, 50-60 Hz, 2 amps (240 V), 5 amps (100 V)

20°-30° C (68-86 F)

230 x 230 [mm] 9 x 9 [in]

0.05 μm 2 μin

1 micron

150 x 150 [mm]

6 x 6 [in]

40 mm

4 in

(adjustable height levels and micrometer fine adjustment)

10 kg

Confocal White Light Sensors Confocal Laser Sensors



### SCAN SUITE 8

### SCAN CT - PROFILE AND 3D ANALYSIS SOFTWARE

SCAN CT is a software package for measuring and analyzing 2D profiles and 3D raster maps.


It offers complete 2D and 3D surface measurement parameters as well as sophisticated filter and compensation methods. All combined in an operator friendly user interface.

#### 2D PROFILE MEASUREMENTS

- Step Height (avg., max. and min. height)
- Flatness and Warpage
- Width and Length


PRODUCT

- Cross Section Area
- Angle, Radius, Contour Analysis



Height and Width Measurement of a solar cell finger


Define base line and measurement areas using reference and measurement cursors. Select analysis from dropdown menu.



Profile analysis on a metal precision part


#### 3D COPLANARITY MEASUREMENTS

- 3D Height (avg., max. and min. height)
- Flatness and Warpage
- Coplanarity




Coplanarity
Measurement of a
BGA Component

Draw rectangle, round or polygon cursors to define base plane and measurement areas.




### PROFILE ROUGHNESS MEASUREMENTS

- DIN EN ISO conform Roughness Parameters
- Shape Removal Algorithm
- Abbott-Firestone Material Curve
- Histogram
- Tip Simulation for Non-Contact Systems




Roughness Measurement on a metal surface

Advanced roughness analysis, even on round or angled surfaces using shape compensation. Display waviness and roughness profile.




#### 3D VOLUME MEASUREMENTS

- Volume (Cuts, Fills, Net Volume)
- Planar area
- Surface area




calculation on a thin film print

Measures cuts and fills and uses height threshold. Accurate areal and planar surface calculations



#### 3D ROUGHNESS MEASUREMENTS

- New DIN EN ISO 25178 Parameters
- 3D Waviness Filters
- 3D Abbott-Firestone material curve, Histogram



Use advanced DIN /TS 16610 Filters. 3D Roughness Analysis even on warped or uneven surfaces.



3D Surface

Roughness

Measurement on a solar wafer


### PARALLEL DATA COLLECTION

- Parallel scanning with up to 4 sensors
- Collect Top, Bottom and Thickness data
- Average Thickness, Bow and Curvature
- **Total Thickness Variation**
- Parallel Intensity Masking



Top, bottom and thickness profile of a solar wafer

Graphical display of thickness maps and top/bottom



Top and bottom surface of a fuel cell


#### SUMMARY

SCAN CT is a complete, unique and easy to use surface analysis software. It offers outstanding features and includes the following highlights:

- Complete 2D and 3D surface analysis
- Profile and 3D roughness measurements according to DIN ISO EN Standards
- Comprehensive profile and surface compensations


#### 2D AND 3D SURFACE COMPENSATIONS

- 2D and 3D Polynom Fit
- Pre- and after measurements
- **Areal Waviness Compensation**




Copper surface defect with areal waviness filter

Surface compensation is only applied based on the data in the reference cursors.




### MORE FEATURES AND HIGHLIGHTS

- x-, y-, z-data stitching capability
- 2D and 3D edge detection algorithm
- Windows 7 64 bit Version available
- Raster up to 200,000,000 data points
- Integrated user management



Automatic detection of BGA bumps

Compare geometry by overlaying profiles.



- Advanced filter technologies
- Uni- / bi-directional scanning
- Linear, circular and ellipsoidal scanning
- Simultaneous data collection of up to 4 sensors
- Dedicated user management
- Up to 200 Mio. data points per raster
- Fast multithread technology